

Art.-Nr.: 10.04.01.00086



SB 1240 260 13.2 IE3-TYP2

The vacuum blower SB is delivered as a ready-to-connect product.


Available accessories: silencer box, dust filter

Technical data

Attribute	Value
Rated power at 60 Hz	13.20 kW
Voltage at 60 Hz	YY230 / Y460 V ± 10 %
Weight	125.000 kg
Suction rate (60 Hz)	1,240.000 m ³ /h
Color	RAL 7035 Light grey
Version	IE3:US/CAN
Vacuum (60 Hz)	260 mbar
Voltage 60 Hz	S067
Approval	UL/CSA

Design data

Attribute	Value
Length L	643.00 mm
Width B1	563.00 mm
Width B	525.00 mm
Height H	611.00 mm
Outside diameter D2	100.0 mm
Thread G1	G4"-F
Hole spacing Y1	400.0 mm
Hole spacing X1	350.0 mm
Thread G5	M8-F



Design data SB 1240 260 13.2 IE3-TYP2



Art.-Nr.: 10.04.01.00086

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 60 Hz	13.20 kW
Voltage at 60 Hz	YY230 / Y460 V ±10 %
Weight	125.000 kg
Suction rate (60 Hz)	1,240.000 m³/h
Version	IE3-US/CAN
Vacuum (60 Hz)	260 mbar
Product family	SB
Version design	IE3-TYP2
Sound pressure level at 60 Hz	79.0 dB(A)
Approval	UL/CSA
Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped	

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.04.01.00086

**Discontinued item**

The product family will be discontinued and is available until **31.12.2025**
 Starting from this time, the article can no longer be ordered.
 alternative article **10.04.01.00187 SB 1240 260 13.2 IE3-TYP2**

**Ordering Data Accessories 10.04.01.00086**

Typ		Item number
Silencer box	SBB-230V-AC-ST-VZ-LUE SB	10.04.04.00239
Silencer box	SBB-24V-DC-ST-VZ-LUE SB	10.04.04.00318
Dust filter	STF 100 P 24.0 SSD	10.07.01.00401
Silencer (round)	SD G2-IG 102x211 SGBL	10.04.04.00163
Silencer (round)	SD R4-AG 205x538 SGBL	10.04.04.00164

