




SB 110 350 1.8 IE3-TYP2

The vacuum blower SB is delivered as a ready-to-connect product.

Available accessories: silencer box, dust filter

Technical data

Attribute	Value
Rated power at 60 Hz	1.80 kW
Voltage at 60 Hz	YY230 / Y460 V ± 10 %
Weight	28.500 kg
Suction rate (60 Hz)	110.000 m ³ /h
Color	RAL 7035 Light grey
Version	IE3:US/CAN
Vacuum (60 Hz)	350 mbar
Voltage 60 Hz	S067
Approval	UL/CSA



Design data SB 110 350 1.8 IE3-TYP2

Design data


Attribute	Value
Length L	431.00 mm
Width B1	317.00 mm
Width B	306.00 mm
Height H	357.00 mm
Outside diameter D2	60.0 mm
Internal diameter d	10.20 mm
Thread G1	G1-1/2"-F
Hole spacing Y1	240.0 mm
Hole spacing X1	240.0 mm

Art.-Nr.: 10.04.01.00089

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 60 Hz	1.80 kW
Voltage at 60 Hz	YY230 / Y460 V ± 10 %
Weight	28.500 kg
Suction rate (60 Hz)	110.000 m ³ /h
Version	IE3-US/CAN
Vacuum (60 Hz)	350 mbar
Product family	SB
Version design	IE3-TYP2
Sound pressure level at 60 Hz	68.4 dB(A)
Approval	UL/CSA

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

**Performance data**

Suction rate at various degrees of evacuation

**Suction rate at various degrees of evacuation**

	0	100	150	200	250	300	330
SB-90-330 (50 Hz)	90	54	41	31	20	10	6
SB-110-350 (60 Hz)	110	73	60	48	37	26	20



Vacuum blower

SB 110 350 1.8 IE3-TYP2



Art.-Nr.: 10.04.01.00089



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.04.01.00089



Ordering Data Accessories 10.04.01.00089

Typ		Item number
Silencer box	SBB-230V-AC-ST/ABS-LUE SB	10.04.04.00234
Silencer box	SBB-24V-DC-ST/ABS-LUE SB	10.04.04.00319
Dust filter	STF 60 P 4.5 SSD	10.07.01.00259
Silencer (round)	SD G1-1/2-AG 113x410 SB	10.04.04.00362
Hose sleeve	ST G1-1/2-AG 38 MS-V	10.08.03.00170
Hose sleeve	ST G1-1/2-AG 60	10.08.03.00349



WWW.SCHMALZ.COM/10.04.01.00089