

Art.-Nr.: 10.04.01.00095




Technical data

Rated power at 60 Hz	4.80 kW
Voltage at 60 Hz	YY230 / Y460 V ±10 %
Weight	62.500 kg
Suction rate (60 Hz)	305.000 m ³ /h
Color	RAL 7035 Light grey
Version	IE3:US/CAN
Vacuum (60 Hz)	400 mbar
Voltage 60 Hz	S067
Approval	UL/CSA

SB 305 400 4.8 IE3-TYP2

The vacuum blower SB is delivered as a ready-to-connect product.

Available accessories: silencer box, dust filter



Design data

Length L	496.00 mm
Width B1	496.00 mm
Width B	474.00 mm
Height H	523.00 mm
Outside diameter D2	60.0 mm
Internal diameter d	12.00 mm
Thread G1	G2"-F
Hole spacing Y1	310.0 mm
Hole spacing X1	310.0 mm

Design data SB 305 400 4.8 IE3-TYP2



Art.-Nr.: 10.04.01.00095




Technical data

Protection type IP	IP 55
Rated power at 60 Hz	4.80 kW
Voltage at 60 Hz	YY230 / Y460 V ±10 %
Weight	62.500 kg
Suction rate (60 Hz)	305.000 m ³ /h
Version	IE3:US/CAN
Vacuum (60 Hz)	400 mbar
Product family	SB
Version design	IE3-TYP2
Sound pressure level at 60 Hz	71.7 dB(A)
Approval	UL/CSA

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped



Performance data



Suction rate at various degrees of evacuation



Suction rate at various degrees of evacuation

	0	100	150	200	250	300	350	400
SB-260-410 (50 Hz)	260	190	160	140	120	95	80	60
SB-305-400 (60 Hz)	305	240	218	190	170	140	120	100



Vacuum blower

SB 305 400 4.8 IE3-TYP2



Art.-Nr.: 10.04.01.00095



Ordering Data Accessories 10.04.01.00095

Typ		Item number
Silencer box	SBB-230V-AC-ST/ABS-LUE SB	10.04.04.00237
Silencer box	SBB-24V-DC-ST/ABS-LUE SB	10.04.04.00322
Dust filter	STF 60 P 6.0 SSD	10.07.01.00260
Silencer kit	SD SB FITTING SD	10.04.04.00363
Silencer (round)	SD G2-AG 115x380 SB	10.04.04.00374
Rubber buffer (round)	GUMM-PUF 101x55 M6-AG SB 3	10.04.04.00385
Hose sleeve	ST G2-AG 60 ST-VZ	10.08.03.00121
Hose sleeve	ST G2-AG 75	10.08.03.00346



WWW.SCHMALZ.COM/10.04.01.00095