

Art.-Nr.: 10.04.01.00119



SB 235 400 3.6 IE3-TYP2 ER


Vacuum blower SB with electro-pneumatic reversing is delivered as a ready to connect product.

Technical data

Attribute	Value
Rated power at 60 Hz	3.60 kW
Voltage at 60 Hz	YY230 / Y460 V ± 10 %
Weight	89.000 kg
Suction rate (60 Hz)	235.000 m ³ /h
Color	RAL 7035 Light grey
Version	IE3:US/CAN
Vacuum (60 Hz)	400 mbar
with	Electro-pneumatic reversing
Approval	UL/CSA

Design data

Attribute	Value
Length L	798.00 mm
Width B1	495.00 mm
Width B	452.00 mm
Height H2	134.00 mm
Height H	504.00 mm
Internal diameter d	13.00 mm
Thread G1	G2"-M
Hole spacing Y1	446.0 mm
Hole spacing X1	435.0 mm



Design data SB 235 400 3.6 IE3-TYP2 ER

Art.-Nr.: 10.04.01.00119



Technical data

Attribute	Value
Protection type IP	IP 55
Max. vacuum	400 mbar
Voltage at 60 Hz	YY230 / Y460 V ± 10 %
Weight	89.000 kg
Product family	SB-ER
Approval	UL/CSA



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.04.01.00119

