

Vacuum blower

SB 260 410 4 IE3



Art.-Nr.: 10.04.01.00126



SB 260 410 4 IE3

The vacuum blower SB is delivered as a ready-to-connect product.


Available assesories: silencer box, dust filter

Technical data

Attribute	Value
Rated power at 50 Hz	4.00 kW
Rated power at 60 Hz	4.80 kW
Voltage at 50 Hz	500 V
Voltage at 60 Hz	Y575V
Weight	62.500 kg
Suction rate (50 Hz)	260.000 m ³ /h
Suction rate (60 Hz)	305.000 m ³ /h
Color	RAL 7035 Light gray
Version	IE3
Vacuum (50 Hz)	410 mbar

Design data

Attribute	Value
Length L	512.00 mm
Width B1	496.00 mm
Width B	474.00 mm
Height H	524.00 mm
Outside diameter D2	60.0 mm
Internal diameter d	12.00 mm
Thread G1	G2"-F
Hole spacing Y1	310.0 mm
Hole spacing X1	310.0 mm



Design data SB 260 410 4 IE3



Vacuum blower

SB 260 410 4 IE3



Art.-Nr.: 10.04.01.00126



Technical data

Attribute	Value
Protection type IP	IP 65
Rated power at 50 Hz	4.00 kW
Rated power at 60 Hz	4.80 kW
Voltage at 50 Hz	500 V
Voltage at 60 Hz	Y575V
Weight	62.500 kg
Suction rate (50 Hz)	260.000 m³/h
Suction rate (60 Hz)	305.000 m³/h
Sound pressure level at 50 Hz	68.9 dB(A)
Version	IE3
Vacuum (50 Hz)	410 mbar
Vacuum (60 Hz)	400 mbar
Product family	SB
Version design	IE3
Sound pressure level at 60 Hz	71.7 dB(A)
Approval	UL/CSA
Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped	



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.04.01.00126



Ordering Data Accessories 10.04.01.00126

Typ		Item number
Silencer box	SBB-230V-AC-ST/ABS-LUE SB	10.04.04.00237
Silencer box	SBB-24V-DC-ST/ABS-LUE SB	10.04.04.00322
Dust filter	STF 60 P 6.0 SSD	10.07.01.00260
Silencer kit	SD SB FITTING SD	10.04.04.00363
Rubber buffer (round)	GUMM-PUF 101x55 M6-AG SB 3	10.04.04.00385
Hose sleeve	ST G2-AG 60 ST-VZ	10.08.03.00121
Hose sleeve	ST G2-AG 75	10.08.03.00346



WWW.SCHMALZ.COM/10.04.01.00126