

Art.-Nr.: 10.04.01.00128



SB 235 400 3.6 IE3-TYP4

The vacuum blower SB is delivered as a ready-to-connect product.


Available accessories: silencer box, dust filter

Technical data

Attribute	Value
Rated power at 60 Hz	3.60 kW
Voltage at 60 Hz	Y575V
Weight	53.500 kg
Suction rate (60 Hz)	235.000 m ³ /h
Color	RAL 7035 Light grey
Version	IE3:CAN
Vacuum (60 Hz)	400 mbar
Voltage 60 Hz	S092
Approval	UL/CSA

Design data

Attribute	Value
Length L	495.00 mm
Width B1	452.00 mm
Width B	390.00 mm
Height H	454.00 mm
Outside diameter D2	60.0 mm
Internal diameter d	12.00 mm
Thread G1	G2"-F
Hole spacing Y1	310.0 mm
Hole spacing X1	310.0 mm



Design data SB 235 400 3.6 IE3-TYP4

Art.-Nr.: 10.04.01.00128

**Technical data**

Attribute	Value
Protection type IP	IP 65
Rated power at 60 Hz	3.60 kW
Voltage at 60 Hz	Y575V
Weight	53.500 kg
Suction rate (60 Hz)	235.000 m ³ /h
Version	IE3:CAN
Vacuum (60 Hz)	400 mbar
Product family	SB
Version design	IE3-TYP4
Approval	UL/CSA

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.04.01.00128**Ordering Data Accessories 10.04.01.00128**

Typ		Item number
Silencer box	SBB-230V-AC-ST/ABS-LUE SB	10.04.04.00236
Silencer box	SBB-24V-DC-ST/ABS-LUE SB	10.04.04.00321
Dust filter	STF 60 P 4.5 SSD	10.07.01.00259
Silencer kit	SD SB FITTING SD	10.04.04.00363
Rubber buffer (round)	GUMM-PUF 101x55 M6-AG SB 3	10.04.04.00385
Hose sleeve	ST G2-AG 60 ST-VZ	10.08.03.00121
Hose sleeve	ST G2-AG 75	10.08.03.00346

