

Art.-Nr.: 10.04.01.00131



SB 390 315 4 IE3-TYP1 ER


Vacuum blower SB with electro-pneumatic reversing is delivered as a ready to connect product.

Technical data

Attribute	Value
Rated power at 50 Hz	4.00 kW
Rated power at 60 Hz	4.80 kW
Voltage at 50 Hz	D230 V / Y400 V ± 10 %
Voltage at 60 Hz	D265 V / Y460 V ± 10 %
Weight	74.500 kg
Suction rate (50 Hz)	390.000 m ³ /h
Suction rate (60 Hz)	470.000 m ³ /h
Color	RAL 7035 Light grey
Version	IE3:EU/CN/IND
Vacuum (50 Hz)	315 mbar

Design data

Attribute	Value
Length L	863.00 mm
Width B1	505.00 mm
Width B	452.00 mm
Height H2	134.00 mm
Height H	504.00 mm
Internal diameter d	13.00 mm
Thread G1	G2-1/2"-M
Hole spacing Y1	446.0 mm
Hole spacing X1	435.0 mm



Design data SB 390 315 4 IE3-TYP1 ER

Art.-Nr.: 10.04.01.00131

**Technical data**

Attribute	Value
Protection type IP	IP 55
Max. vacuum	315 mbar
Rated power at 50 Hz	4.00 kW
Voltage at 50 Hz	D230 V / Y400 V ± 10 %
Voltage at 60 Hz	D265 V / Y460 V ± 10 %
Weight	74.500 kg
Suction rate (50 Hz)	390.000 m ³ /h
Product family	SB-ER
Approval	UL/CSA

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.04.01.00131