

Art.-Nr.: 10.04.01.00139



SB 195 440 3 IE3-TYP3 ER


Vacuum blower SB with electro-pneumatic reversing is delivered as a ready to connect product.

Technical data

Attribute	Value
Rated power at 50 Hz	3.00 kW
Rated power at 60 Hz	3.60 kW
Voltage at 50 Hz	D200 V / Y350 V ± 10 %
Voltage at 60 Hz	D220 V / Y380 - 400 V ± 10 %
Weight	89.000 kg
Suction rate (50 Hz)	195.000 m ³ /h
Suction rate (60 Hz)	235.000 m ³ /h
Color	RAL 7035 Light grey
Version	IE3:JPN/KOR/BRA
Vacuum (50 Hz)	440 mbar

Design data

Attribute	Value
Length L	798.00 mm
Width B1	495.00 mm
Width B	452.00 mm
Height H2	134.00 mm
Height H	504.00 mm
Internal diameter d	13.00 mm
Thread G1	G2"-M
Hole spacing Y1	446.0 mm
Hole spacing X1	435.0 mm



Design data SB 195 440 3 IE3-TYP3 ER



Art.-Nr.: 10.04.01.00139

**Technical data**

Attribute	Value
Protection type IP	IP 55
Max. vacuum	440 mbar
Rated power at 50 Hz	3.00 kW
Voltage at 50 Hz	D200 V / Y350 V ± 10 %
Voltage at 60 Hz	D220 V / Y380 - 400 V ± 10 %
Weight	89.000 kg
Suction rate (50 Hz)	195.000 m ³ /h
Product family	SB-ER

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.04.01.00139