




SB 435 340 6.6 IE3-TYP2 ER

Vacuum blower SB with electro-pneumatic reversing is delivered as a ready to connect product.

Technical data

Rated power at 60 Hz	6.60 kW
Voltage at 60 Hz	YY230 / Y460 V ±10 %
Weight	110.500 kg
Suction rate (60 Hz)	435.000 m ³ /h
Color	RAL 7035 Light grey
Version	IE3:US/CAN
Vacuum (60 Hz)	340 mbar
with	Electro-pneumatic reversing
Approval	UL/CSA



Design data

Length L	1,146.00 mm
Width B1	559.00 mm
Width B	537.00 mm
Height H2	134.00 mm
Height H	646.00 mm
Internal diameter d	13.00 mm
Thread G1	G2-1/2"-M
Hole spacing Y1	506.0 mm
Hole spacing X1	730.0 mm

Design data SB 435 340 6.6 IE3-TYP2 ER

Vacuum blower

SB 435 340 6.6 IE3-TYP2 ER



Art.-Nr.: 10.04.01.00145



Technical data

Protection type IP	IP 55
Max. vacuum	340 mbar
Voltage at 60 Hz	YY230 / Y460 V ± 10 %
Weight	110.500 kg
Product family	SB-ER
Approval	UL/CSA



WWW.SCHMALZ.COM/10.04.01.00145