

Art.-Nr.: 10.04.01.00150




SB 390 245 3.6 IE3-TYP2 ER

Vacuum blower SB with electro-pneumatic reversing is delivered as a ready to connect product.

## Technical data

Rated power at 60 Hz	3.60 kW
Voltage at 60 Hz	YY230 / Y460 V $\pm 10$ %
Weight	78.000 kg
Suction rate (60 Hz)	390.000 m <sup>3</sup> /h
Color	RAL 7035 Light grey
Version	IE3:US/CAN
Vacuum (60 Hz)	245 mbar
with	Electro-pneumatic reversing
Approval	UL/CSA



## Design data

Length L	798.00 mm
Width B1	502.00 mm
Width B	439.00 mm
Height H2	134.00 mm
Height H	476.00 mm
Internal diameter d	13.00 mm
Thread G1	G2"-M
Hole spacing Y1	446.0 mm
Hole spacing X1	435.0 mm

Design data SB 390 245 3.6 IE3-TYP2 ER

Vacuum blower

# SB 390 245 3.6 IE3-TYP2 ER



Art.-Nr.: 10.04.01.00150



## Technical data

Protection type IP	IP 55
Max. vacuum	245 mbar
Voltage at 60 Hz	YY230 / Y460 V $\pm 10$ %
Weight	78.000 kg
Product family	SB-ER
Approval	UL/CSA



[WWW.SCHMALZ.COM/10.04.01.00150](http://WWW.SCHMALZ.COM/10.04.01.00150)