

Art.-Nr.: 10.04.01.00151




SB 470 290 4.8 IE3-TYP2 ER

Vacuum blower SB with electro-pneumatic reversing is delivered as a ready to connect product.

## Technical data

Rated power at 60 Hz	4.80 kW
Voltage at 60 Hz	D230 / Y460 V
Weight	74.500 kg
Suction rate (60 Hz)	470.000 m <sup>3</sup> /h
Color	RAL 7035 Light grey
Version	IE3:US/CAN
Vacuum (60 Hz)	290 mbar
with	Electro-pneumatic reversing
Approval	UL/CSA



Design data SB 470 290 4.8 IE3-TYP2 ER

## Design data

Length L	863.00 mm
Width B1	505.00 mm
Width B	452.00 mm
Height H2	134.00 mm
Height H	504.00 mm
Internal diameter d	13.00 mm
Thread G1	G2-1/2"-M
Hole spacing Y1	446.0 mm
Hole spacing X1	435.0 mm

Vacuum blower

# SB 470 290 4.8 IE3-TYP2 ER



Art.-Nr.: 10.04.01.00151



## Technical data

Protection type IP	IP 55
Max. vacuum	290 mbar
Voltage at 60 Hz	D230 / Y460 V
Weight	74.500 kg
Product family	SB-ER
Approval	UL/CSA



[WWW.SCHMALZ.COM/10.04.01.00151](http://WWW.SCHMALZ.COM/10.04.01.00151)