


Art.-Nr.: 10.04.01.00184



SB 915 280 9 IE3-TYP2

The vacuum blower SB is delivered as a ready-to-connect product.

Available accessories: silencer box, dust filter



Design data SB 915 280 9 IE3-TYP2

Technical data

Attribute	Value
Rated power at 60 Hz	9.00 kW
Voltage at 60 Hz	230 / 460 V - three phase A.C.
Weight	113.000 kg
Suction rate (60 Hz)	915.000 m ³ /h
Color	RAL 7035 Light grey
Version	IE3:US/CAN
Vacuum (60 Hz)	280 mbar
Voltage 60 Hz	230/460AC3
Approval	UL/CSA

Design data

Attribute	Value
Length L1	867.00 mm
Length L	634.00 mm
Width B1	591.00 mm
Width B	496.00 mm
Height H	596.00 mm
Outside diameter D2	100.0 mm
Thread G1	G4"-F
Hole spacing Y1	400.0 mm
Hole spacing X1	350.0 mm
Thread G5	M8-F

Art.-Nr.: 10.04.01.00184

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 60 Hz	9.00 kW
Voltage at 60 Hz	230 / 460 V - three phase A.C.
Weight	113.000 kg
Suction rate (60 Hz)	915.000 m ³ /h
Version	IE3-US/CAN
Vacuum (60 Hz)	280 mbar
Product family	SB
Version design	IE3-TYP2
Sound pressure level at 60 Hz	74.0 dB(A)
Approval	UL/CSA
Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped	

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.04.01.00184**Ordering Data Accessories 10.04.01.00184**

Typ		Item number
Silencer (round)	SD R4-AG 205x538 SGBL	10.04.04.00164
Dust filter	STF 100 P 15.0 SSD	10.07.01.00400
Filter insert (round)	FILT-EINS 220x393 PAP STF-Picl-15	10.07.01.00362

