

Art.-Nr.: 10.04.01.00196



SB 435 340 6.6 IE3-TYP2

The vacuum blower SB is delivered as a ready-to-connect product.


Available assesories: silencer box, dust filter

Technical data

Attribute	Value
Rated power at 60 Hz	6.60 kW
Voltage at 60 Hz	D265 V / Y460 V ± 10 %
Weight	89.000 kg
Suction rate (60 Hz)	435.000 m ³ /h
Color	RAL 7035 Light grey
Version	IE3:US/CAN
Vacuum (60 Hz)	340 mbar
Voltage 60 Hz	S065
Approval	UL/CSA

Design data

Attribute	Value
Length L1	817.00 mm
Length L	583.00 mm
Width B1	545.00 mm
Width B	496.00 mm
Height H	596.00 mm
Outside diameter D2	76.0 mm
Thread G1	G4"-F
Hole spacing Y1	400.0 mm
Hole spacing X1	350.0 mm
Thread G5	M8-F



Design data SB 435 340 6.6 IE3-TYP2



Art.-Nr.: 10.04.01.00196

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 60 Hz	6.60 kW
Voltage at 60 Hz	D265 V / Y460 V $\pm 10\%$
Weight	89.000 kg
Suction rate (60 Hz)	435.000 m ³ /h
Version	IE3-US/CAN
Vacuum (60 Hz)	340 mbar
Product family	SB
Version design	IE3-TYP2
Sound pressure level at 60 Hz	69.0 dB(A)
Approval	UL/CSA
Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped	

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.04.01.00196**Ordering Data Accessories 10.04.01.00196**

Typ		Item number
Silencer (round)	SD R4-AG 205x538 SGBL	10.04.04.00164
Dust filter	STF 75 P 8.0 SSD	10.07.01.00263
Filter insert (round)	FILT-EINS 3 159x376 STF-Picl-8	10.07.01.00079

