

Art.-Nr.: 10.05.01.00052




Technical data

Attribute	Value
Nominal size	12.00 mm
Weight	1.200 kg
Voltage DC	230 V - AC
Pressure range (operating pressure) [bar]	-0.95 ... 0.00 bar
Function valve	3/2 multiway valve
Connection thread	G1/2"-F
Control valve	Normally closed

EMVO 12 230V-AC 3/2 NC

Solenoid valve EMVO is delivered as a ready-to-connect product.

Available accessories: venting filter



Design data

Attribute	Value
Length L2	32.00 mm
Length L	122.00 mm
Height H1	135.50 mm
Height H	60.00 mm
Outside diameter D	80.00 mm
Internal diameter d	6.50 mm
Thread G1	G1/2"-F
Thread G2	G1/2"-F
Hole spacing Y1	40.0 mm
Hole spacing X1	24.0 mm

Design data EMVO 12 230V-AC 3/2 NC

Art.-Nr.: 10.05.01.00052

**Technical data**

Attribute	Value
Nominal size	12.00 mm
Weight	1.200 kg
Closing time	82.0 ms
Voltage DC	230 V - AC
Pressure range (operating pressure) [bar]	-0.95 ... 0.00 bar
Product family	EMVO
Control valve	Normally closed

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.01.00052**Ordering Data Accessories 10.05.01.00052**

Typ	Item number
Filter with mounting kit	FAS 80x33.8 G1/2-AG 10.05.01.00061

