



Art.-Nr.: 10.05.01.00053



EMVO 20 230V-AC 3/2 NC

Solenoid valve EMVO is delivered as a ready-to-connect product.

Available accessories: venting filter



Design data EMVO 20 230V-AC 3/2 NC

Technical data

Attribute	Value
Nominal size	20.00 mm
Weight	5.800 kg
Voltage DC	230 V - AC
Pressure range (operating pressure) [bar]	-0.95 ... 0.00 bar
Function valve	3/2 multiway valve
Connection thread	G3/4"-F
Control valve	Normally closed

Design data

Attribute	Value
Length L2	43.00 mm
Length L	206.00 mm
Height H1	187.50 mm
Height H	100.00 mm
Outside diameter D	80.00 mm
Internal diameter d	9.00 mm
Thread G1	G3/4"-F
Thread G2	G3/4"-F
Height H3	10.00 mm
Hole spacing Y1	80.0 mm

Art.-Nr.: 10.05.01.00053

**Technical data**

Attribute	Value
Nominal size	20.00 mm
Weight	5.800 kg
Closing time	208.0 ms
Voltage DC	230 V - AC
Pressure range (operating pressure) [bar]	-0.95 ... 0.00 bar
Product family	EMVO
Control valve	Normally closed

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.01.00053**Ordering Data Accessories 10.05.01.00053**

Typ	Item number
Filter with mounting kit	FAS 80x39 G3/4-AG 10.05.01.00062

