

Art.-Nr.: 10.05.01.00066



EMV 3 24V-DC 2/2 NC

Solenoid valve EMV is delivered as a ready-to-connect product.


Available accessories: venting filter

Technical data

Attribute	Value
Nominal size	3.00 mm
Power consumption DC	4.8 W
Weight	0.200 kg
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	-1.00 ... 9.00 bar
Function valve	2/2 multiway valve
Connection thread	G1/4"-F
Control valve	Normally closed
Nenndurchfluss bei 0,1 bar	1.300 m ³ /h

Design data

Attribute	Value
Length L	42.00 mm
Width B1	61.50 mm
Width B2	47.00 mm
Height H1	60.00 mm
Height H	22.00 mm
Thread G1	G1/4"-F
Thread length LG1	12.0 mm
Thread length LG5	5.0 mm
Thread G5	M3-F



Design data EMV 3 24V-DC 2/2 NC

Art.-Nr.: 10.05.01.00066

**Technical data**

Attribute	Value
Nominal size	3.00 mm
Power consumption DC	4.8 W
Weight	0.200 kg
Closing time	20.0 ms
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	-1.00 ... 9.00 bar
Product family	EMV
Control valve	Normally closed
Nenndurchfluss bei 0,1 bar	1.300 m ³ /h

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.01.00066