

Art.-Nr.: 10.05.01.00069



EMV 5 230V-AC 3/2 NO

Solenoid valve EMV is delivered as a ready-to-connect product.


Available accessories: venting filter

Technical data

Attribute	Value
Nominal size	5.00 mm
Weight	0.518 kg
Voltage DC	230 V - AC
Pressure range (operating pressure) [bar]	-1.00 ... 1.00 bar
Function valve	3/2 multiway valve
Connection thread	G1/4"-F
Control valve	Normally open
Nennndurchfluss bei 0,1 bar	2.100 m³/h

Design data

Attribute	Value
Length L1	76.00 mm
Length L	46.00 mm
Width B	32.00 mm
Height H1	118.00 mm
Height H	71.00 mm
Outside diameter D	56.00 mm
Thread G1	G1/4"-F
Thread G2	G1/4"-F
Hole spacing Y1	24.0 mm
Hole spacing X1	38.0 mm



Design data EMV 5 230V-AC 3/2 NO

Art.-Nr.: 10.05.01.00069

**Technical data**

Attribute	Value
Nominal size	5.00 mm
Weight	0.518 kg
Closing time	20.0 ms
Voltage DC	230 V - AC
Pressure range (operating pressure) [bar]	-1.00 ... 1.00 bar
Product family	EMV
Control valve	Normally open
Nenndurchfluss bei 0,1 bar	2.100 m ³ /h

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.01.00069**Ordering Data Accessories 10.05.01.00069**

Typ		Item number
Filter with mounting kit	FAS 63x19 G1/4-AG	10.05.01.00060

**Ordering Data Spare Parts 10.05.01.00069**

Typ		Item number
Filter with mounting kit	FAS 63x19 G1/4-AG	10.05.01.00060

