



Art.-Nr.: 10.05.01.00070



EMV 10 24V-DC 3/2 NO

Solenoid valve EMV is delivered as a ready-to-connect product.

Available accessories: venting filter



Design data EMV 10 24V-DC 3/2 NO

Technical data

Attribute	Value
Nominal size	10.00 mm
Power consumption DC	36.2 W
Weight	2.510 kg
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	-1.00 ... 15.00 bar
Function valve	3/2 multiway valve
Connection thread	G1/2"-F
Control valve	Normally open
Nennndurchfluss bei 0,1 bar	16.000 m ³ /h

Design data

Attribute	Value
Length L1	174.50 mm
Length L	166.50 mm
Width B1	98.50 mm
Width B	62.00 mm
Height H1	108.00 mm
Height H	79.00 mm
Outside diameter D	80.00 mm
Internal diameter d	7.00 mm
Thread G1	G1/2"-F
Thread G2	G1/2"-F

Art.-Nr.: 10.05.01.00070

**Technical data**

Attribute	Value
Nominal size	10.00 mm
Power consumption DC	36.2 W
Weight	2.510 kg
Closing time	40.0 ms
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	-1.00 ... 15.00 bar
Product family	EMV
Control valve	Normally open
Nenndurchfluss bei 0,1 bar	16.000 m ³ /h

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.01.00070**Ordering Data Accessories 10.05.01.00070**

Typ		Item number
Filter with mounting kit	FAS 80x33.8 G1/2-AG	10.05.01.00061

**Ordering Data Spare Parts 10.05.01.00070**

Typ		Item number
Filter with mounting kit	FAS 80x33.8 G1/2-AG	10.05.01.00061

