


Solenoid valve

EMV 15 230V-AC 3/2 NO



Art.-Nr.: 10.05.01.00073




EMV 15 230V-AC 3/2 NO

Solenoid valve EMV is delivered as a ready-to-connect product.

Available accessories: venting filter

Technical data

Attribute	Value
Nominal size	15.00 mm
Weight	4.665 kg
Voltage DC	230 V - AC
Pressure range (operating pressure) [bar]	-1.00 ... 15.00 bar
Function valve	3/2 multiway valve
Connection thread	G3/4\"-F
Control valve	Normally open
Nominal flow at 0.1 bar	40.000 m ³ /h



Design data EMV 15 230V-AC 3/2 NO

Design data

Attribute	Value
Length L1	211.00 mm
Length L	209.00 mm
Height H1	140.00 mm
Height H	114.00 mm
Outside diameter D	80.00 mm
Internal diameter d	6.50 mm
Thread G1	G3/4\"-F
Thread G2	G3/4\"-F
Hole spacing Y1	40.0 mm
Thread spacing X1	133.0 mm
Thread G3	G3/4\"-F



WWW.SCHMALZ.COM/10.05.01.00073

Art.-Nr.: 10.05.01.00073

**Technical data**

Attribute	Value
Nominal size	15.00 mm
Weight	4.665 kg
Closing time	80.0 ms
Voltage DC	230 V - AC
Pressure range (operating pressure) [bar]	-1.00 ... 15.00 bar
Product family	EMV
Control valve	Normally open
Nominal flow at 0.1 bar	40.000 m³/h

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.01.00073**Ordering Data Accessories 10.05.01.00073**

Typ		Item number
Filter with mounting kit	FAS 80x39 G3/4-AG	10.05.01.00062

**Ordering Data Spare Parts 10.05.01.00073**

Typ		Item number
Filter with mounting kit	FAS 80x39 G3/4-AG	10.05.01.00062
Sealing kit	DI-SET EMV 15	10.05.01.00460

