


Art.-Nr.: 10.05.01.00077



EMV 25 230V-AC 3/2 NO

Solenoid valve EMV is delivered as a ready-to-connect product.


Available accessories: venting filter

Technical data

Attribute	Value
Nominal size	25.00 mm
Weight	9.600 kg
Voltage DC	230 V - AC
Pressure range (operating pressure) [bar]	-1.00 ... 15.00 bar
Function valve	3/2 multiway valve
Connection thread	G1-1/4"-F
Control valve	Normally open
Nominal flow at 0.1 bar	91.200 m ³ /h

Design data

Attribute	Value
Length L1	271.50 mm
Length L	281.00 mm
Height H1	200.00 mm
Height H	167.00 mm
Outside diameter D	80.00 mm
Internal diameter d	8.50 mm
Thread G1	G1-1/4"-F
Thread G2	G1-1/4"-F
Hole spacing Y1	50.0 mm
Thread spacing X1	178.0 mm
Thread G3	G1-1/4"-F



Design data EMV 25 230V-AC 3/2 NO

Art.-Nr.: 10.05.01.00077

**Technical data**

Attribute	Value
Nominal size	25.00 mm
Weight	9.600 kg
Closing time	130.0 ms
Voltage DC	230 V - AC
Pressure range (operating pressure) [bar]	-1.00 ... 15.00 bar
Product family	EMV
Control valve	Normally open
Nominal flow at 0.1 bar	91.200 m ³ /h

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.01.00077**Ordering Data Accessories 10.05.01.00077**

Typ		Item number
Filter with mounting kit	FAS 80x32 G1-1/4-AG EMVP-25+50	10.05.01.00064

**Ordering Data Spare Parts 10.05.01.00077**

Typ		Item number
Filter with mounting kit	FAS 80x32 G1-1/4-AG EMVP-25+50	10.05.01.00064
Sealing kit	DI-SET EMV 25	10.05.01.00462

