

Art.-Nr.: 10.05.01.00278




Technical data

Attribute	Value
Nominal size	1.10 mm
Power consumption DC	1.0 W
Weight	0.038 kg
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	bar
Function valve	3/2 multiway valve
Control valve	Normally open

EMV 1.1 24V-DC 3/2 NO H

Solenoid valve EMV is delivered as a ready-to-connect product.

Available accessories: venting filter



Design data

Attribute	Value
Length L1	8.40 mm
Length L	42.00 mm
Width B1	15.00 mm
Height H1	31.00 mm
Height H	20.50 mm
Internal diameter d	3.20 mm
Hole spacing X1	9.7 mm

Design data EMV 1.1 24V-DC 3/2 NO H



Art.-Nr.: 10.05.01.00278



Technical data

Attribute	Value
Nominal size	1.10 mm
Power consumption DC	1.0 W
Weight	0.038 kg
Closing time	12.0 ms
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	bar
Product family	EMV
Control valve	Normally open



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.01.00278

