

Art.-Nr.: 10.05.01.00288



EMV 1.5 24V-DC 3/2 NC K-2P

Solenoid valve EMV is delivered as a ready-to-connect product.


Available accessories: venting filter

Technical data

Attribute	Value
Nominal size	1.50 mm
Power consumption DC	2.8 W
Weight	0.065 kg
Voltage DC	24 V - DC
Interface electrical connection	Cable, 2-pole
Pressure range (operating pressure) [bar]	2.5 ... 7.0 bar
Function valve	3/2 multiway valve
Connection thread	M5-M
Control valve	Normally closed

Design data

Attribute	Value
Length L1	46.50 mm
Length L	43.10 mm
Width B1	26.60 mm
Width B2	8.10 mm
Internal diameter d	4.00 mm
Thread G1	M5-M
Thread G2	M5-F



Design data EMV 1.5 24V-DC 3/2 NC K-2P



Art.-Nr.: 10.05.01.00288



Technical data

Attribute	Value
Nominal size	1.50 mm
Power consumption DC	2.8 W
Weight	0.065 kg
Closing time	12.0 ms
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	2.5 ... 7.0 bar
Product family	EMV
Control valve	Normally closed



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.01.00288

