


Art.-Nr.: 10.05.01.00289



EMV 2.5 24V-DC 3/2 NC K-2P

Solenoid valve EMV is delivered as a ready-to-connect product.

Available accessories: venting filter



Design data EMV 2.5 24V-DC 3/2 NC K-2P

Technical data

Attribute	Value
Nominal size	2.50 mm
Power consumption DC	4.5 W
Weight	0.100 kg
Voltage DC	24 V - DC
Interface electrical connection	Cable, 2-pole
Pressure range (operating pressure) [bar]	2.0 ... 8.0 bar
Function valve	3/2 multiway valve
Connection thread	G1/8"-M
Control valve	Normally closed

Design data

Attribute	Value
Length L1	56.50 mm
Length L	51.70 mm
Width B1	31.70 mm
Width B2	10.70 mm
Internal diameter d	4.00 mm
Thread G1	G1/8"-M
Thread G2	M5-F



Art.-Nr.: 10.05.01.00289



Technical data

Attribute	Value
Nominal size	2.50 mm
Power consumption DC	4.5 W
Weight	0.100 kg
Closing time	18.0 ms
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	2.0 ... 8.0 bar
Product family	EMV
Control valve	Normally closed



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.01.00289

