


Art.-Nr.: 10.05.01.00290



EMV 2 24V-DC 3/2 NC

Solenoid valve EMV is delivered as a ready-to-connect product.

Available accessories: venting filter



Design data EMV 2 24V-DC 3/2 NC

Technical data

Attribute	Value
Nominal size	2.00 mm
Power consumption DC	2.4 W
Weight	0.150 kg
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	-1.00 ... 8.00 bar
Function valve	3/2 multiway valve
Connection thread	G1/8"-F
Control valve	Normally closed
Neenddurchfluss bei 0,1 bar	0.400 m³/h

Design data

Attribute	Value
Length L	68.00 mm
Width B	25.00 mm
Height H	70.00 mm
Thread G1	G1/8"-F
Thread G2	G1/8"-F
Hole spacing Y1	16.0 mm
Hole spacing X1	30.0 mm
Thread G5	M5-F



Art.-Nr.: 10.05.01.00290

**Technical data**

Attribute	Value
Nominal size	2.00 mm
Power consumption DC	2.4 W
Weight	0.150 kg
Closing time	12.0 ms
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	-1.00 ... 8.00 bar
Product family	EMV
Control valve	Normally closed
Nenndurchfluss bei 0,1 bar	0.400 m ³ /h

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.01.00290