

Art.-Nr.: 10.05.01.00366




EMV 3 24V-DC 2/2 NC K-2P

Technical data

Attribute	Value
Length L	64.50 mm
Internal diameter d	6.00 mm

Design data

Attribute	Value
Length L1	72.00 mm
Length L	64.50 mm
Width B1	36.00 mm
Width B2	12.80 mm
Internal diameter d	6.00 mm
Thread G1	G1/4\"-M
Thread G2	G1/8\"-F



Design data EMV 3 24V-DC 2/2 NC K-2P



Art.-Nr.: 10.05.01.00366



Technical data

Attribute	Value
Power consumption DC	5.4 W
Weight	0.153 kg
Nominal flow rate	10.500 m³/h
Pressure range (operating pressure) [bar]	2.0 ... 8.0 bar
Operating temperature	°C
Control valve	Normally closed
Voltage	24V - DC



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.01.00366

