

Solenoid valve

EMVP 32 24V-DC 3/2 NO



Art.-Nr.: 10.05.02.00068



EMVP 32 24V-DC 3/2 NO


Solenoid valve EMVP is delivered as a ready-to-connect product.

Available accessories: venting filter, connection cable for solenoid valves, socket with M12 connection

Technical data

Attribute	Value
Nominal size	32.00 mm
Weight	0.500 kg
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	-0.95 ... 0.00 bar
Function valve	3/2 multiway valve
Connection thread	G1-1/4"-F
Control valve	Normally open
Nenndurchfluss bei 0,1 bar	121.400 m³/h

Design data



Design data EMVP 32 24V-DC 3/2 NO

Attribute	Value
Length L1	200.50 mm
Length L	160.00 mm
Width B1	101.00 mm
Width B2	61.50 mm
Width B	90.50 mm
Height H	101.00 mm
Outside diameter D	80.00 mm
Thread G1	G1-1/4"-F
Thread G2	G1-1/4"-F
Hole spacing X1	33.0 mm



Art.-Nr.: 10.05.02.00068

**Technical data**

Attribute	Value
Nominal size	32.00 mm
Power consumption DC	9.8 W
Weight	0.500 kg
Closing time	300.0 ms
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	-0.95 ... 0.00 bar
Product family	EMVP
Control valve	Normally open
Nenndurchfluss bei 0,1 bar	121.400 m³/h

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.02.00068**Ordering Data Accessories 10.05.02.00068**

Typ		Item number
Filter with mounting kit	FAS 80x39 G3/4-AG	10.05.01.00062
Plug	STEC 4 S-M12-4 St	10.05.02.00157
Hose sleeve	ST G2-AG 60 ST-VZ	10.08.03.00121
Hose clamp	SSD 65-70 ST-VZ	10.07.10.00098

