

Art.-Nr.: 10.05.02.00074



EMVP 32 230V-AC 3/2 NO


Solenoid valve EMVP is delivered as a ready-to-connect product.

Available accessories: venting filter, connection cable for solenoid valves, socket with M12 connection

Technical data

Attribute	Value
Nominal size	32.00 mm
Weight	0.500 kg
Voltage DC	230 V - AC
Pressure range (operating pressure) [bar]	-0.95 ... 0.00 bar
Function valve	3/2 multiway valve
Connection thread	G1-1/4"-F
Control valve	Normally open
Nominal flow at 0.1 bar	121.400 m³/h

Design data



Design data EMVP 32 230V-AC 3/2 NO

Attribute	Value
Length L1	203.50 mm
Length L	163.00 mm
Width B1	101.00 mm
Width B2	61.50 mm
Width B	90.50 mm
Height H	101.00 mm
Outside diameter D	80.00 mm
Thread G1	G1-1/4"-F
Thread G2	G1-1/4"-F
Hole spacing X1	33.0 mm



Art.-Nr.: 10.05.02.00074

**Technical data**

Attribute	Value
Nominal size	32.00 mm
Weight	0.500 kg
Closing time	300.0 ms
Voltage DC	230 V - AC
Pressure range (operating pressure) [bar]	-0.95 ... 0.00 bar
Product family	EMVP
Control valve	Normally open
Nominal flow at 0.1 bar	121.400 m³/h

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.02.00074**Ordering Data Accessories 10.05.02.00074**

Typ		Item number
Filter with mounting kit	FAS 80x39 G3/4-AG	10.05.01.00062

