

Art.-Nr.: 10.05.02.00144




Technical data

Attribute	Value
Nominal size	10.00 mm
Weight	0.420 kg
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	-0.95 ... 5.00 bar
Function valve	3/2 multiway valve
Connection thread	G3/8"-F
Control valve	Optional NO / NC
Nennndurchfluss bei 0,1 bar	19.300 m ³ /h

EMVP 10 24V-DC 3/2 NO/NC

Solenoid valve EMVP is delivered as a ready-to-connect product.

Available accessories: venting filter, connection cable for solenoid valves, socket with M12 connection



Design data

Attribute	Value
Length L1	117.00 mm
Length L2	19.50 mm
Length L	50.00 mm
Width B1	67.00 mm
Width B	35.00 mm
Height H1	154.50 mm
Height H2	32.80 mm
Height H	147.00 mm
Outside diameter D	56.00 mm
Internal diameter d	4.30 mm

Design data EMVP 10 24V-DC 3/2 NO/NC



Art.-Nr.: 10.05.02.00144

**Technical data**

Attribute	Value
Nominal size	10.00 mm
Power consumption DC	5.0 W
Weight	0.420 kg
Closing time	22.0 ms
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	-0.95 ... 5.00 bar
Product family	EMVP
Control valve	Optional NO / NC
Nenndurchfluss bei 0,1 bar	19.300 m ³ /h

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.02.00144**Ordering Data Accessories 10.05.02.00144**

Typ		Item number
Filter with mounting kit	FAS 63x47 G3/8-AG EMVP-10	10.05.01.00065
Plug	STEC 4 S-M12-4 St	10.05.02.00157

**Ordering Data Wear Parts 10.05.02.00144**

Typ		Item number
Set of parts subject to wear	VST EMVP	10.05.02.00331
Valve coil	SPULE 24V-DC	10.05.02.00340
Outlet socket	STEC-DOSE-24V-DC	10.05.02.00337

