

Art.-Nr.: 10.05.02.00146




EMVP 15 24V-DC 3/2 NO/NC

Solenoid valve EMVP is delivered as a ready-to-connect product.

Available accessories: venting filter, connection cable for solenoid valves, socket with M12 connection

Technical data

Attribute	Value
Nominal size	15.00 mm
Weight	0.390 kg
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	-0.95 ... 5.00 bar
Function valve	3/2 multiway valve
Connection thread	G1/2"-F
Control valve	Optional NO / NC
Nenndurchfluss bei 0,1 bar	39.700 m ³ /h



Design data EMVP 15 24V-DC 3/2 NO/NC

Design data

Attribute	Value
Length L1	111.50 mm
Length L	75.00 mm
Width B1	77.50 mm
Width B2	37.50 mm
Width B	75.00 mm
Height H1	173.80 mm
Height H2	22.50 mm
Height H	166.30 mm
Outside diameter D	80.00 mm
Internal diameter d	6.50 mm



Art.-Nr.: 10.05.02.00146

**Technical data**

Attribute	Value
Nominal size	15.00 mm
Power consumption DC	5.3 W
Weight	0.390 kg
Closing time	90.0 ms
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	-0.95 ... 5.00 bar
Product family	EMVP
Control valve	Optional NO / NC
Nenndurchfluss bei 0,1 bar	39.700 m ³ /h

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.02.00146**Ordering Data Accessories 10.05.02.00146**

Typ		Item number
Plug	STEC 4 S-M12-4 St	10.05.02.00157
Filter with mounting kit	FAS 80x33.8 G1/2-AG	10.05.01.00061

**Ordering Data Wear Parts 10.05.02.00146**

Typ		Item number
Set of parts subject to wear	VST EMVP	10.05.02.00332
Valve coil	SPULE 24V-DC	10.05.02.00340
Outlet socket	STEC-DOSE-24V-DC	10.05.02.00337

