

Art.-Nr.: 10.05.02.00151




EMVP 25 24V-DC 3/2 NO/NC

Solenoid valve EMVP is delivered as a ready-to-connect product.

Available accessories: venting filter, connection cable for solenoid valves, socket with M12 connection

Technical data

Attribute	Value
Nominal size	25.00 mm
Weight	0.520 kg
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	-0.95 ... 5.00 bar
Function valve	3/2 multiway valve
Connection thread	G1"-F
Control valve	Optional NO / NC
Nenndurchfluss bei 0,1 bar	90.100 m ³ /h



Design data EMVP 25 24V-DC 3/2 NO/NC

Design data

Attribute	Value
Length L1	132.00 mm
Length L	94.00 mm
Width B1	87.00 mm
Width B2	47.00 mm
Width B	94.00 mm
Height H1	195.50 mm
Height H2	22.00 mm
Height H	189.50 mm
Outside diameter D	80.00 mm
Internal diameter d	8.00 mm

Art.-Nr.: 10.05.02.00151

**Technical data**

Attribute	Value
Nominal size	25.00 mm
Power consumption DC	7.0 W
Weight	0.520 kg
Closing time	80.0 ms
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	-0.95 ... 5.00 bar
Product family	EMVP
Control valve	Optional NO / NC
Nenndurchfluss bei 0,1 bar	90.100 m ³ /h

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.02.00151**Ordering Data Accessories 10.05.02.00151**

Typ		Item number
Filter with mounting kit	FAS 80x38 G1-AG EMVP	10.05.01.00063
Plug	STEC 4 S-M12-4 St	10.05.02.00157

