

Art.-Nr.: 10.05.02.00163




EMVP 5 24V-DC 5/2 IMP

Solenoid valve EMVP is delivered as a ready-to-connect product.

Available accessories: venting filter, connection cable for solenoid valves, socket with M12 connection

Technical data

Attribute	Value
Nominal size	5.00 mm
Weight	193.000 kg
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	-0.95 ... 0.00 bar
Function valve	5/2 multiway valve
Connection thread	G1/8"-F
Control valve	Impulse valve
Nennndurchfluss bei 0,1 bar	4.800 m³/h



Design data EMVP 5 24V-DC 5/2 IMP

Design data

Attribute	Value
Length L1	37.00 mm
Length L	32.00 mm
Width B2	15.20 mm
Width B	15.20 mm
Height H2	76.30 mm
Height H	152.70 mm
Internal diameter d	4.30 mm
Thread G1	G1/8"-F
Thread G2	G1/8"-F
Height H3	30.00 mm

Art.-Nr.: 10.05.02.00163

**Technical data**

Attribute	Value
Nominal size	5.00 mm
Power consumption DC	2.4 W
Weight	193.000 kg
Closing time	13.0 ms
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	-0.95 ... 0.00 bar
Product family	EMVP
Control valve	Impulse valve
Nenndurchfluss bei 0,1 bar	4.800 m ³ /h

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.02.00163**Ordering Data Accessories 10.05.02.00163**

Typ		Item number
Connection cable	ASK B-Form-C 5000 K-3P	21.04.06.00084

