

Solenoid valve

EMVP 50 230V-AC 3/2 NC



Art.-Nr.: 10.05.02.00171



EMVP 50 230V-AC 3/2 NC


Solenoid valve EMVP is delivered as a ready-to-connect product.

Available accessories: venting filter, connection cable for solenoid valves, socket with M12 connection

Technical data

Attribute	Value
Nominal size	50.00 mm
Weight	1.360 kg
Voltage DC	230 V - AC
Pressure range (operating pressure) [bar]	-0.95 ... 0.00 bar
Function valve	3/2 multiway valve
Connection thread	G2"-F
Control valve	Normally closed

Design data



Attribute	Value
Length L1	260.00 mm
Length L	225.00 mm
Width B1	151.00 mm
Width B2	105.50 mm
Width B	114.00 mm
Height H	142.00 mm
Outside diameter D	80.00 mm
Thread G1	G2"-F
Thread G2	G2"-F
Hole spacing X1	49.0 mm

Design data EMVP 50 230V-AC 3/2 NC



WWW.SCHMALZ.COM/10.05.02.00171

Art.-Nr.: 10.05.02.00171

**Technical data**

Attribute	Value
Nominal size	50.00 mm
Power consumption DC	5.0 W
Weight	1.360 kg
Closing time	500.0 ms
Voltage DC	230 V - AC
Pressure range (operating pressure) [bar]	-0.95 ... 0.00 bar
Product family	EMVP
Control valve	Normally closed

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.02.00171**Ordering Data Accessories 10.05.02.00171**

Typ		Item number
Welded nipple	ANSW-NIP G2x70 ST-VZ	10.01.10.02811

