

Art.-Nr.: 10.05.02.00198




Technical data

Attribute	Value
Nominal size	32.00 mm
Weight	0.500 kg
Voltage DC	24 V - DC
Pressure range (operating pressure) [bar]	-0.95 ... 0.00 bar
Function valve	3/2 multiway valve
Connection thread	G1-1/4"-F
Control valve	Normally closed

EMVP 32 24V-DC 3/2 NC

Solenoid valve EMVP is delivered as a ready-to-connect product.

Available accessories: venting filter, connection cable for solenoid valves, socket with M12 connection



Design data

Attribute	Value
Length L1	200.50 mm
Length L	160.00 mm
Width B1	101.00 mm
Width B2	61.50 mm
Width B	90.50 mm
Height H	101.00 mm
Outside diameter D	80.00 mm
Thread G1	G1-1/4"-F
Thread G2	G1-1/4"-F
Thread G3	G3/4-IG

Design data EMVP 32 24V-DC 3/2 NC



Art.-Nr.: 10.05.02.00198

**Technical data**

Attribute	Value
Nominal size	32.00 mm
Power consumption DC	0.5 W
Weight	0.500 kg
Closing time	300.0 ms
Voltage DC	24 V - DC
Nominal flow rate	130.000 m ³ /h
Product family	EMVP
Control valve	Normally closed

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.02.00198