Solenoid valve

EMVP 8 24V-DC 5/3 NO

Art.-Nr.: 10.05.02.00246

EMVP 8 24V-DC 5/3 NO

Technical data

Attribute	Value
Nominal size	8.00 mm
Voltage DC	24 V - DC
Nominal flow rate	42.000 m³/h
Pressure range (operating pressure) [bar]	3.00 ... 10.00 bar
Operating temperature	°C
Control pressure range [bar]	3.0 ... 10.0
Thread G1	G1/8"-F
Connection thread	G1/8"-F
Control valve	Normally open
Voltage	24V - DC

Design data

Attribute	Value
Length L1	213.80 mm
Length L	175.60 mm
Width B	16.80 mm
Height H1	58.70 mm
Height H	40.80 mm
Internal diameter d	4.50 mm
Thread G1	G1/8"-F
Thread G2	G1/8"-F
Hole spacing X1	19.0 mm
Thread G3	G1/8"-F

Design data EMVP 8 24V-DC 5/3 NO

Further documentation

CAD data and other documents relating to the article can be found at: **www.schmalz.com/10.05.02.00246**

Contact Schmalz: J. Schmalz GmbH, Johannes-Schmalz-Str. 1 • 72293 Glatten • +49 7443 2403-105 • kundencenter@schmalz.de