

Check valve

SVV G1/4-IG



Art.-Nr.: 10.05.03.00003




SVV G1/4-IG

Check valves SVK, SVKG, SVV are delivered as a ready-to-connect product.

Technical data

Attribute	Value
Thread G1	G1/4"-M
Thread G2	G1/4"-F



Design data SVV G1/4-IG

Design data

Attribute	Value
Length L	42.50 mm
Width B	23.90 mm
Thread G1	G1/4"-M
Thread length LG1	8.0 mm
Thread G2	G1/4"-F
Thread length LG2	11.0 mm
Key width SW1	17.0 mm



Art.-Nr.: 10.05.03.00003

**Technical data**

Attribute	Value
Weight	24.70 g
Required suction capacity for $p_u = -0.3$ bar	1.360 m ³ /h
Required suction capacity for $p_u = -0.6$ bar	1.720 m ³ /h
Flow rate max. vacuum	400.0 l/min
Flow rate max.	24.000 m ³ /h
Product family	SVK

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.03.00003