

Art.-Nr.: 10.05.03.00035



SVK G1/4-IG


Check valves SVK, SVKG, SVV are delivered as a ready-to-connect product.

Technical data

Attribute	Value
Thread G1	G1/4"-M
Thread G2	G1/4"-F

Design data

Attribute	Value
Length L	26.00 mm
Thread G1	G1/4"-M
Thread length LG1	10.0 mm
Thread G2	G1/4"-F
Thread length LG2	11.0 mm
Key width SW1	17.0 mm



Design data SVK G1/4-IG

Art.-Nr.: 10.05.03.00035

**Technical data**

Attribute	Value
Weight	17.5 g
Required suction capacity for $p_u = -0.3$ bar	0.170 m ³ /h
Required suction capacity for $p_u = -0.6$ bar	0.200 m ³ /h
Flow rate max.	20.400 m ³ /h
Product family	SVK
Flow rate max. pressure	340.0 l/min

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.03.00035