





SVN G1/4-AG N018

Check valve SVN is delivered as a ready-to-connect product.



Design data SVN G1/4-AG N018

Technical data

Attribute	Value
Thread G1	G1/4"-M
Key width SW1	17.0 mm
Interface nipple family	N018

Design data

Attribute	Value
Length L1	29.00 mm
Length L	5.00 mm
Outside diameter D2	9.0 mm
Outside diameter D	14.00 mm
Thread G1	G1/4"-M
Thread length LG1	11.0 mm
Key width SW1	17.0 mm

Art.-Nr.: 10.05.03.00054

**Technical data**

Attribute	Value
Weight	8.0 g
Required suction capacity for $p_u = -0.3$ bar	2.300 m ³ /h
Required suction capacity for $p_u = -0.6$ bar	3.300 m ³ /h
Flow rate max. vacuum	450.0 l/min
Flow rate max.	27.000 m ³ /h
Product family	SVN

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.03.00054