

Vacuum regulator

VR G1/4-IG HW



Art.-Nr.: 10.05.05.00075




VR G1/4-IG HW

Vacuum regulator VR is delivered as a ready-to-connect product, including holding angle.

Technical data

Attribute	Value
Vacuum range	-950 ... -25 mbar
Thread G1	G1/4"-F
Additional equipment	Holding angle



Design data VR G1/4-IG HW

Design data

Attribute	Value
Length L	84.00 mm
Width B1	60.00 mm
Width B2	40.00 mm
Width B	40.00 mm
Height H2	95.70 mm
Height H	109.00 mm
Internal diameter d	24.00 mm
Thread G1	G1/4"-F
Thread G2	G1/4"-F
Height H3	7.00 mm



Vacuum regulator
VR G1/4-IG HW



Art.-Nr.: 10.05.05.00075



Technical data

Attribute	Value
Weight	0.200 kg
Repeatability	± 2% of full-scale value
Flow rate max. vacuum	140.0 l/min
Flow rate max.	8.400 m ³ /h
Operating temperature	5 ... 60 °C
Vacuum range	-950 ... -25 mbar
Product family	VR



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.05.00075



WWW.SCHMALZ.COM/10.05.05.00075