




HSV 8 3/2 G3/8-IG

Manual slide valve HSV is delivered as a ready-to-connect product.



Design data HSV 8 3/2 G3/8-IG

## Technical data

| Attribute                                 | Value               |
|-------------------------------------------|---------------------|
| Nominal size                              | 8.00 mm             |
| Pressure range (operating pressure) [bar] | -0.95 ... 10.00 bar |
| Thread G1                                 | G3/8"-F             |
| Function valve                            | 3/2 multiway valve  |

## Design data

| Attribute           | Value    |
|---------------------|----------|
| Length L            | 70.70 mm |
| Outside diameter D1 | 35.0 mm  |
| Thread G1           | G3/8"-F  |
| Thread length LG1   | 15.0 mm  |
| Key width SW1       | 22.0 mm  |

Manuel slide valve

## HSV 8 3/2 G3/8-IG



Art.-Nr.: 10.05.07.00035



### Technical data

| Attribute         | Value       |
|-------------------|-------------|
| Nominal size      | 8.00 mm     |
| Weight            | 0.156 kg    |
| Nominal flow rate | 10.000 m³/h |
| Product family    | HSV         |



### Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.05.07.00035](http://www.schmalz.com/10.05.07.00035)



[WWW.SCHMALZ.COM/10.05.07.00035](http://WWW.SCHMALZ.COM/10.05.07.00035)