


Art.-Nr.: 10.05.08.00001



KVD 6 3/2

Three-way ball valve KVD is delivered as a ready-to-connect product.



Design data KVD 6 3/2

## Technical data

| Attribute                                 | Value               |
|-------------------------------------------|---------------------|
| Nominal size                              | 6.00 mm             |
| Pressure range (operating pressure) [bar] | -0.95 ... 16.00 bar |
| Thread G1                                 | G1/4"-F             |
| Function valve                            | 3/2 multiway valve  |

## Design data

| Attribute           | Value     |
|---------------------|-----------|
| Length L2           | 125.00 mm |
| Length L            | 77.00 mm  |
| Width B             | 58.00 mm  |
| Height H            | 85.00 mm  |
| Outside diameter D1 | 39.0 mm   |
| Thread G1           | G1/4"-F   |
| Thread length LG1   | 19.0 mm   |
| Key width SW1       | 22.0 mm   |

Ball valve

## KVD 6 3/2



Art.-Nr.: 10.05.08.00001



### Technical data

| Attribute         | Value                   |
|-------------------|-------------------------|
| Nominal size      | 6.00 mm                 |
| Weight            | 0.081 kg                |
| Nominal flow rate | 5.000 m <sup>3</sup> /h |
| Product family    | KVD                     |



### Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.05.08.00001](http://www.schmalz.com/10.05.08.00001)



[WWW.SCHMALZ.COM/10.05.08.00001](http://WWW.SCHMALZ.COM/10.05.08.00001)