


Art.-Nr.: 10.05.08.00004



KVD 20 3/2

Three-way ball valve KVD is delivered as a ready-to-connect product.



Design data KVD 20 3/2

Technical data

Attribute	Value
Nominal size	20.00 mm
Pressure range (operating pressure) [bar]	-0.95 ... 16.00 bar
Thread G1	G3/4"-F
Function valve	3/2 multiway valve

Design data

Attribute	Value
Length L2	145.00 mm
Length L	92.00 mm
Width B	70.00 mm
Height H	107.00 mm
Outside diameter D1	47.0 mm
Thread G1	G3/4"-F
Thread length LG1	23.0 mm
Key width SW1	34.0 mm

Ball valve

KVD 20 3/2



Art.-Nr.: 10.05.08.00004



Technical data

Attribute	Value
Nominal size	20.00 mm
Weight	1.260 kg
Nominal flow rate	45.000 m³/h
Product family	KVD



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.08.00004



WWW.SCHMALZ.COM/10.05.08.00004