


Art.-Nr.: 10.05.08.00005



KVD 25 3/2

Three-way ball valve KVD is delivered as a ready-to-connect product.



Design data KVD 25 3/2

Technical data

Attribute	Value
Nominal size	25.00 mm
Pressure range (operating pressure) [bar]	-0.95 ... 16.00 bar
Thread G1	G1"-F
Function valve	3/2 multiway valve

Design data

Attribute	Value
Length L2	170.00 mm
Length L	104.00 mm
Width B	80.00 mm
Height H	124.00 mm
Outside diameter D1	55.0 mm
Thread G1	G1"-F
Thread length LG1	25.0 mm
Key width SW1	41.0 mm

Ball valve

KVD 25 3/2



Art.-Nr.: 10.05.08.00005



Technical data

Attribute	Value
Nominal size	25.00 mm
Weight	1.930 kg
Nominal flow rate	55.000 m³/h
Product family	KVD



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.08.00005



WWW.SCHMALZ.COM/10.05.08.00005