




Technical data

Attribute	Value
Connection	Tube Ø4
Measuring range [bar]	-1,00 ... 0,00 bar
Cable length Lk	3.0 m

VS-V-SA STR4

Vacuum switch VS-V-SA is delivered as a ready-to-connect product.



Design data

Attribute	Value
Length L	21.00 mm
Width B	9.50 mm
Height H1	32.20 mm
Height H2	9.90 mm
Height H	17.20 mm
Outside diameter D	4.00 mm
Cable length Lk	3.0 m

Design data VS-V-SA STR4



Art.-Nr.: 10.06.02.00226

**Technical data**

Attribute	Value
Inputs / outputs	Analog: 1...5 V
Electrical connection	Cable
Protection type IP	IP 40
Measuring range	bar
Max. overpressure safety	5.0 bar
Weight	5.0 g
Measured medium	Non-aggressive gases; dry, oil-free air
Temperature influence	± 3% of full-scale value
Repeatability	± 1% of full-scale value
Connection	Tube Ø4
Product family	VS-V-SA
Voltage	10-24V DC

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.06.02.00226

