

Art.-Nr.: 10.06.02.00260




VS-V-SD 60 STR6

Vacuum switch VS-V-SD is delivered as a ready-to-connect product.

Technical data

Attribute	Value
Switching point	- 600
Connection	Tube Ø6
Measuring range [bar]	-1,0 ... 0,0 bar
Cable length Lk	3.0 m



Design data VS-V-SD 60 STR6

Design data

Attribute	Value
Length L	21.00 mm
Width B	9.50 mm
Height H1	37.20 mm
Height H2	9.90 mm
Height H	17.20 mm
Outside diameter D	6.00 mm
Cable length Lk	3.0 m



Art.-Nr.: 10.06.02.00260

**Technical data**

Attribute	Value
Inputs / outputs	1 digital
Electrical connection	Cable
Protection type IP	IP 40
Max. overpressure safety	5.0 bar
Weight	5.0 g
Indication	LED
Hysteresis	Fixed: approx. 20 mbar
Measured medium	Non-aggressive gases; dry, oil-free air
Temperature influence	± 3% of full-scale value
Repeatability	± 1% of full-scale value
Switching point	- 600
Switching capacity max.	60 mA
Connection	Tube Ø6
Measuring range [bar]	-1,0 ... 0,0 bar
Operating temperature	0 ... 50 °C
Product family	VS-V-SD
Voltage	10-24V DC

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.06.02.00260