

Art.-Nr.: 10.06.02.00292




VS-V-AV-T-PNP M8-4 S

Vacuum and pressure switch VS-V/P-AH/AV-T is delivered as a ready-to-connect product (without connection cable).

Available accessories: connection cable, connection adapter

Technical data

Attribute	Value
Construction vacuum switch	PNP switching
Inputs / outputs	2 digital
Electrical connection	Male connect M8, 4 pole
Protection type IP	IP 40
Indication	LED
Measuring range [bar]	-1,0 ... 0,0 bar
Shape	Vertical adaptation
Switching point setting	Teach function
with	fixed hysteresis



Design data VS-V-AV-T-PNP M8-4 S

Design data

Attribute	Value
Length L1	48.00 mm
Length L	41.20 mm
Width B	10.00 mm
Height H	16.40 mm
Thread G1	M8-M

Art.-Nr.: 10.06.02.00292

**Technical data**

Attribute	Value
Inputs / outputs	2 digital
Electrical connection	Male connect M8, 4 pole
Protection type IP	IP 40
Max. overpressure safety	5.0 bar
Current consumption	20.00 mA
Weight	6.0 g
Indication	LED
Hysteresis	Fixed: approx. 20 mbar
Measured medium	Non-aggressive gases; dry, oil-free air
Temperature influence	± 3% of full-scale value
Repeatability	± 1% of full-scale value
Switching capacity max.	200 mA
Measuring range [bar]	-1,0 ... 0,0 bar
Operating temperature	0 ... 60 °C
Product family	VS-V-AH
Voltage	10-30V DC

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.06.02.00292**Ordering Data Accessories 10.06.02.00292**

Typ		Item number
Connection cable	ASK WB-M8-4 5000 K-4P	10.06.02.00032
Connection cable	ASK B-M8-4 5000 K-4P	10.06.02.00031
Connection adapter VS	ADAP-VS 6-1.3x16	10.06.02.00300
Connection adapter VS	ADAP-VS M5-AG-1.3x16	10.06.02.00299

