


Art.-Nr.: 10.06.02.00425



BEF-WIN 13x50x31 1.6 VS

**Technical data**

| Attribute          | Value         |
|--------------------|---------------|
| Utilization design | Vacuum switch |
| Length L           | 31.00 mm      |
| Width B            | 13.00 mm      |
| Height H           | 50.00 mm      |
| Wall thickness s   | 1.60 mm       |



Design data BEF-WIN 13x50x31 1.6 VS

**Design data**

| Attribute            | Value    |
|----------------------|----------|
| Length L2            | 40.00 mm |
| Length L             | 31.00 mm |
| Width B2             | 20.30 mm |
| Width B              | 13.00 mm |
| Height H2            | 5.70 mm  |
| Height H             | 50.00 mm |
| Internal diameter d1 | 4.2 mm   |
| Internal diameter d  | 4.30 mm  |
| Wall thickness s     | 1.60 mm  |
| Hole spacing X1      | 20.0 mm  |



**Technical data**

| Attribute       | Value |
|-----------------|-------|
| Measuring range | bar   |

Mounting bracket

## BEF-WIN 13x50x31 1.6 VS



Art.-Nr.: 10.06.02.00425



**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.06.02.00425](http://www.schmalz.com/10.06.02.00425)



[WWW.SCHMALZ.COM/10.06.02.00425](http://WWW.SCHMALZ.COM/10.06.02.00425)