

Vacuum/pressure switch

VSi VP8 D M8-4



Art.-Nr.: 10.06.02.00579



VSi VP8 D M8-4

Technical data


Attribute	Value
Construction vacuum switch	with display
Electrical connection	Male connect M8, 4 pole
Protection type IP	IP 65
Indication	2xLED
Measuring range [bar]	-1,0 ... 8,0 bar

Vacuum and pressure switch VSi is delivered as a ready-to-connect product (without connection cable). The product consists of:

- Vacuum and pressure switch of type VSi - available as vacuum version, pressure version or combined version without display or with integrated display

Available accessories: connection cable, mounting bracket

Design data



Attribute	Value
Length L1	77.50 mm
Length L	60.50 mm
Outside diameter D	19.60 mm
Thread G1	G1/8"-M
Thread length LG1	8.0 mm
Thread G2	M5-F
Thread G3	M8x1-M

Design data VSi VP8 D M8-4



WWW.SCHMALZ.COM/10.06.02.00579

Vacuum/pressure switch
VSi VP8 D M8-4



Art.-Nr.: 10.06.02.00579



Technical data

Attribute	Value
Construction vacuum switch	with display
Inputs / outputs	2 digital
Electrical connection	Male connect M8, 4 pole
Protection type IP	IP 65
Max. overpressure safety	174.04 psi
Current consumption	35.00 mA
Weight	16.0 g
Indication	2xLED
Hysteresis	Adjustable
Measured medium	Non-aggressive gases; dry, oil-free air
Repeatability	± 3% of full-scale value
Switching capacity max.	100 mA
Connection	G1/8"-M + M5-F
Measuring range [bar]	-1,0 ... 8,0 bar
Operating temperature	0 ... 50 °C
Measuring range	-14.5 ... 116.0 psi
Product family	VSi
Voltage	10-30V DC



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.06.02.00579



Ordering Data Accessories 10.06.02.00579

Typ		Item number
Connection cable	ASK B-M8-4 5000 K-4P	10.06.02.00031
Connection cable	ASK WB-M8-4 5000 K-4P	10.06.02.00032
Mounting bracket	BEF-WIN 21x22x60.5 1.5 VS	10.06.02.00061
Plug union, straight	STVI-GE G1/8-IG 4	10.08.02.00149
Plug union, straight	STVI-GE G1/8-IG 6	10.08.02.00150
Plug union, straight	STVI-GE G1/8-IG 8	10.08.02.00151
Holder VSi	HTR-VSi Clip	10.06.02.00718
Mounting bracket	BEF-WIN 21x22x61.5 1.5 VSi-D-M8	10.06.02.00664



WWW.SCHMALZ.COM/10.06.02.00579