


Art.-Nr.: 10.06.04.00003



FS 10 D 2NA K

The product is delivered as a ready to connect component.

A 3 m long cable with open strands is included.



Design data FS 10 D 2NA K

Technical data

Attribute	Value
Construction vacuum switch	2x NPN + 1x analog
Electrical connection	Cable
Protection type IP	IP 40 (with plug)
Measuring range	-1...8bar
Connection	G1/8"
Shape	Digital display
Flow in vacuum range	0 ... 10 l/min
Flow in pressure range	0 ... 10 l/min

Design data

Attribute	Value
Length L1	76.20 mm
Length L2	18.50 mm
Length L	55.00 mm
Width B	17.00 mm
Height H1	52.00 mm
Height H2	3.00 mm
Height H	50.00 mm
Internal diameter d1	2.5 mm
d2	3.0 mm
Thread G1	G1/8"-F

Art.-Nr.: 10.06.04.00003

**Technical data**

Attribute	Value
Construction vacuum switch	2x NPN + 1x analog
Electrical connection	Cable
Protection type IP	IP 40 (with plug)
Measuring range	-1...8bar
Weight	107.0 g
Connection	G1/8"
Product family	FS
Flow in vacuum range	0 ... 10 l/min
Flow in pressure range	0 ... 10 l/min

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.06.04.00003**Ordering Data Accessories 10.06.04.00003**

Typ	Item number
Mounting bracket	BEF-WIN 33.6x5x40 1
	10.06.04.00011

