


Art.-Nr.: 10.06.04.00010



FS 200 D 2PA K

The product is delivered as a ready to connect component.

A 3 m long cable with open strands is included.



Design data FS 200 D 2PA K

## Technical data

| Attribute                  | Value              |
|----------------------------|--------------------|
| Construction vacuum switch | 2x PNP + 1x analog |
| Electrical connection      | Cable              |
| Protection type IP         | IP 40 (with plug)  |
| Measuring range            | -1...8bar          |
| Connection                 | G1/4"              |
| Shape                      | Digital display    |
| Flow in vacuum range       | 0 ... 100 l/min    |
| Flow in pressure range     | 0 ... 200 l/min    |

## Design data

| Attribute            | Value    |
|----------------------|----------|
| Length L1            | 84.20 mm |
| Length L2            | 18.50 mm |
| Length L             | 55.00 mm |
| Width B              | 17.00 mm |
| Height H1            | 52.00 mm |
| Height H2            | 3.00 mm  |
| Height H             | 50.00 mm |
| Internal diameter d1 | 2.5 mm   |
| d2                   | 3.0 mm   |
| Thread G1            | G1/4"-F  |



Art.-Nr.: 10.06.04.00010

**Technical data**

| Attribute                  | Value              |
|----------------------------|--------------------|
| Construction vacuum switch | 2x PNP + 1x analog |
| Electrical connection      | Cable              |
| Protection type IP         | IP 40 (with plug)  |
| Measuring range            | -1...8bar          |
| Weight                     | 110.5 g            |
| Connection                 | G1/4"              |
| Product family             | FS                 |
| Flow in vacuum range       | 0 ... 100 l/min    |
| Flow in pressure range     | 0 ... 200 l/min    |

**Further documentation**CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.06.04.00010](http://www.schmalz.com/10.06.04.00010)**Ordering Data Accessories 10.06.04.00010**

| Typ              | Item number         |
|------------------|---------------------|
| Mounting bracket | BEF-WIN 33.6x5x40 1 |
|                  | 10.06.04.00011      |

