




VF-10 G3/8-IG 50

Vacuum filter VF / STF / STF-D is delivered as a ready to connect product.

Available spare parts: replacement filter cartridge
Available accessories: mounting bracket

Technical data

Attribute	Value
Filter pore size	50.0 µm
Nominal flow rate	10.000 m³/h
Connection	G3/8"-F
Shape	Aluminum housing



Design data VF-10 G3/8-IG 50

Design data

Attribute	Value
Length L1	157.00 mm
Length L2	42.00 mm
Length L	70.00 mm
Height H2	30.00 mm
Height H	54.00 mm
Outside diameter D	48.00 mm
Thread G1	G3/8"-F

Art.-Nr.: 10.07.01.00004

**Technical data**

Attribute	Value
Max. vacuum	-950 mbar
Filter pore size	50.0 µm
Weight	0.215 kg
Nominal flow rate	10.000 m³/h
Connection	G3/8"-F
Product family	VF

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.01.00004**Ordering Data Accessories 10.07.01.00004**

Typ	Item number
Mounting bracket	BEF-WIN 42x36x48 2 PVT-PVS 10.07.01.00011

**Ordering Data Spare Parts 10.07.01.00004**

Typ	Item number
Filter insert (round)	FILT-EINS 50 28x51 PAP VF-3/8 10.07.01.00014

**Ordering Data Wear Parts 10.07.01.00004**

Typ	Item number
Filter insert (round)	FILT-EINS 50 28x51 PAP VF-3/8 10.07.01.00014

